


表.1 : FlowCon SM 最高流量設定

U15-25.Low 1/2",3/4",1" 15,20,25A 33-300kPaD		U25-40.Low 1",1-1/4",1-1/2" 25,32,40A 33-300kPaD		W50.Low & W65-80.Low 2", 2.1/2",3" 50,65,80A 50-300kPaD		W50.High & W65-80.High 2", 2.1/2",3" 50,65,80A 80-400kPaD		最高流量 ディップスイッチ設定						全閉までの ステム 回転数	全回転動作 の 時間
L/min	L/sec	L/min	L/sec	L/min	L/sec	L/min	L/sec	1	2	3	4	5	6	回転数	秒
9.66	0.161	31.98	0.533	138.0	2.30	175.8	2.93	ON	ON	ON	ON	ON	ON	1	30
10.68	0.178	35.16	0.586	145.2	2.42	184.8	3.08	OFF	ON	ON	ON	ON	ON	1.1	33
11.64	0.194	38.40	0.640	152.4	2.54	193.8	3.23	ON	OFF	ON	ON	ON	ON	1.2	36
12.66	0.211	41.58	0.693	160.2	2.67	202.8	3.38	OFF	OFF	ON	ON	ON	ON	1.3	39
13.62	0.227	44.82	0.747	167.4	2.79	211.8	3.53	ON	ON	OFF	ON	ON	ON	1.4	42
14.64	0.244	48.00	0.800	174.6	2.91	220.8	3.68	OFF	ON	OFF	ON	ON	ON	1.5	45
15.60	0.260	50.52	0.842	182.4	3.04	229.8	3.83	ON	OFF	OFF	ON	ON	ON	1.6	48
16.56	0.276	53.04	0.884	190.2	3.17	239.4	3.99	OFF	OFF	OFF	ON	ON	ON	1.7	51
17.52	0.292	55.56	0.926	197.4	3.29	248.4	4.14	ON	ON	ON	OFF	ON	ON	1.8	54
18.48	0.308	58.08	0.968	205.2	3.42	258.0	4.30	OFF	ON	ON	OFF	ON	ON	1.9	57
19.44	0.324	60.60	1.010	213.0	3.55	267.0	4.45	ON	OFF	ON	OFF	ON	ON	2	60
20.34	0.339	63.00	1.050	219.6	3.66	274.8	4.58	OFF	OFF	ON	OFF	ON	ON	2.1	63
21.24	0.354	64.80	1.080	225.6	3.76	282.6	4.71	ON	ON	OFF	OFF	ON	ON	2.2	66
22.20	0.370	67.20	1.120	232.2	3.87	290.4	4.84	OFF	ON	OFF	OFF	ON	ON	2.3	69
23.10	0.385	69.00	1.150	238.2	3.97	298.2	4.97	ON	OFF	OFF	OFF	ON	ON	2.4	72
24.00	0.400	71.40	1.190	244.8	4.08	306.0	5.10	OFF	OFF	OFF	OFF	ON	ON	2.5	75
24.84	0.414	73.20	1.220	250.2	4.17	313.2	5.22	ON	ON	ON	ON	OFF	ON	2.6	78
25.74	0.429	75.00	1.250	255.6	4.26	319.8	5.33	OFF	ON	ON	ON	OFF	ON	2.7	81
26.58	0.443	77.40	1.290	260.4	4.34	327.0	5.45	ON	OFF	ON	ON	OFF	ON	2.8	84
27.48	0.458	79.20	1.320	265.8	4.43	333.6	5.56	OFF	OFF	ON	ON	OFF	ON	2.9	87
28.32	0.472	81.00	1.350	271.2	4.52	340.8	5.68	ON	ON	OFF	ON	OFF	ON	3	90
29.04	0.484	82.80	1.380	275.4	4.59	346.2	5.77	OFF	ON	OFF	ON	OFF	ON	3.1	93
29.76	0.496	84.60	1.410	280.2	4.67	351.6	5.86	ON	OFF	OFF	ON	OFF	ON	3.2	96
30.54	0.509	85.80	1.430	284.4	4.74	357.0	5.95	OFF	OFF	OFF	ON	OFF	ON	3.3	99
31.26	0.521	87.60	1.460	289.2	4.82	362.4	6.04	ON	ON	ON	OFF	OFF	ON	3.4	102
31.98	0.533	89.40	1.490	293.4	4.89	367.8	6.13	OFF	ON	ON	OFF	OFF	ON	3.5	105
32.58	0.543	91.20	1.520	297.6	4.96	372.6	6.21	ON	OFF	ON	OFF	OFF	ON	3.6	108
33.18	0.553	93.00	1.550	301.2	5.02	378.0	6.30	OFF	OFF	ON	OFF	OFF	ON	3.7	111
33.78	0.563	94.20	1.570	305.4	5.09	382.8	6.38	ON	ON	OFF	OFF	OFF	ON	3.8	114
34.38	0.573	96.00	1.600	309.0	5.15	388.2	6.47	OFF	ON	OFF	OFF	OFF	ON	3.9	117
34.98	0.583	97.80	1.630	313.2	5.22	393.0	6.55	ON	OFF	OFF	OFF	OFF	ON	4	120
35.52	0.592	99.00	1.650	316.8	5.28	397.2	6.62	OFF	OFF	OFF	OFF	OFF	ON	4.1	123
36.06	0.601	100.2	1.670	319.8	5.33	402.0	6.70	ON	ON	ON	ON	ON	OFF	4.2	126
36.60	0.610	102.0	1.700	323.4	5.39	406.2	6.77	OFF	ON	ON	ON	ON	OFF	4.3	129
37.14	0.619	103.2	1.720	326.4	5.44	411.0	6.85	ON	OFF	ON	ON	ON	OFF	4.4	132
37.68	0.628	104.4	1.740	330.0	5.50	415.2	6.92	OFF	OFF	ON	ON	ON	OFF	4.5	135
38.10	0.635	105.6	1.760	333.0	5.55	419.4	6.99	ON	ON	OFF	ON	ON	OFF	4.6	138
38.52	0.642	106.8	1.780	336.6	5.61	424.2	7.07	OFF	ON	OFF	ON	ON	OFF	4.7	141
39.00	0.650	108.0	1.800	339.6	5.66	428.4	7.14	ON	OFF	OFF	ON	ON	OFF	4.8	144
39.42	0.657	109.2	1.820	343.2	5.72	433.2	7.22	OFF	OFF	OFF	ON	ON	OFF	4.9	147
39.84	0.664	110.4	1.840	346.2	5.77	437.4	7.29	ON	ON	ON	OFF	ON	OFF	5	150
40.20	0.670	111.6	1.860	349.2	5.82	441.0	7.35	OFF	ON	ON	OFF	ON	OFF	5.1	153
40.56	0.676	112.8	1.880	352.2	5.87	445.2	7.42	ON	OFF	ON	OFF	ON	OFF	5.2	156
40.92	0.682	113.4	1.890	355.8	5.93	448.8	7.48	OFF	OFF	ON	OFF	ON	OFF	5.3	159
41.28	0.688	114.6	1.910	358.8	5.98	453.0	7.55	ON	ON	OFF	OFF	ON	OFF	5.4	162
41.64	0.694	115.8	1.930	361.8	6.03	456.6	7.61	OFF	ON	OFF	OFF	ON	OFF	5.5	165
42.00	0.700	117.0	1.950	366.0	6.10	462.0	7.70	ON	OFF	OFF	OFF	ON	OFF	5.6	168
42.30	0.705	117.6	1.960	370.8	6.18	467.4	7.79	OFF	OFF	OFF	OFF	ON	OFF	5.7	171
42.66	0.711	118.8	1.980	375.0	6.25	472.2	7.87	ON	ON	ON	ON	OFF	OFF	5.8	174
42.96	0.716	119.4	1.990	379.8	6.33	477.6	7.96	OFF	ON	ON	ON	OFF	OFF	5.9	177
43.32	0.722	120.6	2.010	384.0	6.40	483.0	8.05	ON	OFF	ON	ON	OFF	OFF	6	180

FlowCon
international
A Griswold-Frese Company



U.S.A. : 124A East Dyer Rd, Santa Ana, C.A, 92707, USA, Ph : + 714 754 5898, Fax : +714 754 5899.

Denmark : Sorovej 8, 4200 Slagelse, Denmark, Ph : +45 58 56 00 90, Fax : + 45 58 56 00 91

Singapore : 37, Geylang Lorong 23, Yu Li Industrial Building, #04-04, Singapore, 388371, Ph : +65 841 8849/50, Fax : +65 841 88 43

総輸入発売元



株式会社 **日本フロー・コントロールズ**

Apr 1998